

Lote	Modelo	Nome do produto	Cidade	Estado
AS2936D1305	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	RIO DE JANEIRO	Rio de Janeiro
AS2938D1305	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	ITAJAI	Santa Catarina
AS5158D1611	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	TUBARÃO	Santa Catarina
AS5283D1708	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	PORTO VELHO	Rondônia
AS5346D1710	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	RIO DE JANEIRO	Rio de Janeiro
AS5188D1702	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	SAO PAULO	São Paulo
AS5345D1710	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	CURITIBA	Paraná
AS2918D1305	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	GOIANIA	Goiás
AS3320D1403	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	SÃO PAULO	São Paulo
AS3297D1402	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	SALVADOR	Bahia
AS5150D1611	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	BOTUCATU	São Paulo
AS3306D1403	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	SALVADOR	Bahia
AS3281D1402	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	JOINVILLE	Santa Catarina
AS3333D1403	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	FORTALEZA	Ceará
AS3323D1403	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	VITORIA	Espírito San
AS3282D1402	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	BARUERI	São Paulo
AS3314D1403	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	SÃO PAULO	São Paulo
AS3731D1410	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	PORTO ALEGRE	Rio Grande do Sul
AS3308D1403	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	SÃO PAULO	São Paulo
AS3330D1403	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	BRASILIA	Brasília
AS3270D1402	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	SÃO PAULO	São Paulo
AS3317D1403	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	BARRETOS	São Paulo
AS3269D1402	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	BARRETOS	São Paulo
AS3329D1403	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	SALVADOR	Bahia
AS2919D1305	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	SOROCABA	São Paulo
AS2917D1305	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	ARACATUBA	São Paulo
AS2920D1305	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	PELOTAS	Rio Grande do Sul
AS2852D1303	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	PORTO ALEGRE	Rio Grande do Sul
AS2921D1305	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	SÃO PAULO	São Paulo
AS2933D1305	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	FORTALEZA	Ceará
AS5307D1711	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	LONDRINA	Paraná
S38-0337-01	S380031	AUTOSTAINER PLUS	SÃO PAULO	São Paulo

AS2934D1305	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	BELÉM	Para
AS5733D1907	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	FORTALEZA	Ceará
AS5580D1901	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	BARRETOS	São Paulo
AS1510D0910	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	SÃO PAULO	São Paulo
AS2813D1302	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	CUIABA	Mato Grosso
AS2603D1209	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	SANTA BARBARA DOESTE	São Paulo
AS1631D1005	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	SÃO PAULO	São Paulo
AS1541D1001	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	RIO DE JANEIRO	Rio de Janeiro
AS1400D0908	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	PORTO ALEGRE	Rio Grande do Sul
AS1704D1008	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	NATAL	Rio Grande do Norte
AS1617D1005	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	CURITIBA	Paraná
AS1676D1007	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	SALVADOR	Bahia
AS1731D1009	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	SÃO PAULO	São Paulo
AS1733D1009	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	BOTUCATU	São Paulo
AS1771D1010	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	FORTALEZA	Ceará
AS1625D1005	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	SÃO PAULO	São Paulo
AS1050D0811	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	SÃO PAULO	São Paulo
AS2814D1302	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	SÃO PAULO	São Paulo
AS3001D1307	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	PORTO VELHO	Rondônia
AS3003D1307	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	CAXIAS DO SUL	Rio Grande do Sul
AS1049D0811	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	PORTO ALEGRE	Rio Grande do Sul
S38-7753-01	S380031	AUTOSTAINER PLUS	BRASÍLIA	Brasília
AS5149D1611	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	SAO PAULO	São Paulo
AS5284D1708	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	SAO PAULO	São Paulo
AS5712D1906	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	CURITIBA	Paraná
AS5731D1907	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	BELO HORIZONTE	Minas Gerais
AS5713D1906	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	JOÃO PESSOA	Paraíba
AS5716D1906	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	SÃO PAULO	São Paulo
AS5736D1907	AS48030	AUTOSTAINER LINK 48 INSTRUMENT SYSTEM	DIVINOPOLIS	Minas Gerais